WooCommerce PDF Catalog





Prosthetic Universal Kit

<u>Read More</u>	
SKU:	
Price:	[].[] 120
Stock:	instock
Categories:	Devices

Product Description

Dental Implant Prosthetic Universal Kit

- Made up of high quality medical grade stainless steel
- One piece construction, well polished
- Total 16 drivers compatible with different implant system
- Torque wrench with torque values from 15-70Ncm
- 135°C autoclavable
- Color coded drivers for easy identification
- **Implant Prosthetic Kit** includes a complete set of components for tightening clinical and prosthetic screws to the correct torque value. This kit give clinicians the ability to handle any implant brand attachment. Save time and money by not having to order drivers from many different companies. The Universal Prosthetic Kit is composed of various prosthetic drivers that are compatible to different brands and sizes of implant abutments. A lever style torque wrench is included which is capable of measuring torque value from 15-70Ncm. Drivers can be easily grabbed and used by hand when needed. The color coding of the drivers makes the selection of the appropriate driver easy and intuitive.
- Indications:
- This Universal Prosthetic Kit is used when implanting a fixture in a place where a tooth is missing, or when connecting or detaching a cover screw or other upper structures.

This kit will cover all implant types

- Straumann
- Anthogyr
- Ankylo
- Roott
- Osstem
- Cortax
- Dentium
- Nobel
- biohorizon

WooCommerce PDF Catalog



Rogin Dental i Cure Curing Light

Read More SKU: Price: [..] 70 Stock: instock Categories: Devices

Developer By PDF Catalog Woocommerce

WooCommerce PDF Catalog

Product Description

Rogin Dental i Cure Curing Light



ROGIN DENTAL OBTURATION PEN

Read MoreSKU:Price:[].[] 50Stock:instockCategories:Devices

Product Description

Naturalldent Dental Obturation Pen with Charging Base, Gutta Percha Obturation System Endo Heated Pen with 2 Tips



Rogin E-LITE ES Endo Extractor System

Endo Extractor System

<u>Read More</u>	
SKU:	
Price:	<u>□.□ 220</u> Original price was: 220 <u>□.□.□.195</u> Current price is: 195 <u>[].</u>].
Stock:	instock
Categories:	Devices

Product Description

The **Rogin E-LITE ES Endo Extractor System** is designed for use during root canal treatment. It assists in removing broken root canal files. Here are the key details about this system:

• Components:

- Extractor Shank: The central component.
- **Extractors**: Three different sizes: ET-80 (0.80 mm outer diameter, 0.50 mm inner diameter), ET-90 (0.90 mm outer diameter, 0.60 mm inner diameter), and ET-110 (1.10 mm outer diameter, 0.70 mm inner diameter).
- Access Files: Five sizes with varying outer diameters (AF-60, AF-70, AF-80, AF-90, AF-110) and a working length of 19 mm.
- **Shaping Reamers and Trephine Drills**: Available in three sizes (SR-80/TD-80, SR-90/TD-90, SR-110/TD-110) with different outer diameters and inner diameters.
- Wrench: Included for ease of use.



Surgery Motor

[video width="852" height="480" mp4="https://ecodentstores.com/wp-content/uploads/2024/09/Self-Pum ping-Cooling-Water-Dental-Implant-Brushless-Motor-Irrigation-Surgical.mp4"][/video]

Read More SKU: Price: [].[] 195 Stock: instock Categories: <u>Devices</u>

Product Description

Dental Surgical and implant brushless motor system Brushless motor Torque: 17N.cm for 1:1 contra angle, and 50Ncm for 20:1 contra angle Rotation speed 0-50,000r/min Cooling water: 0-100ml/min Self-pumping water **Specification**:

opeemeanon	
Motor type	Direct current brushless motor
Voltage	DC36V
Operation mode	REV
Speed	2000-50,000 rpm
Torque	17N·cm
Sterilization	121°C20 minute,or 135°C12 minute
Motor size	Φ23×L145mm
Noise	≤60dB
Control unit:	
Model	EM1-A
Voltage	110-220V[]
Motor size	L225×W90×H100mm
Fuse protector	T3.15AL250V
Water spray:	
Cooling water supply	0-100ml/min

Maintenance: Use alcohol to wipe the motor and control panel everyday to keep it clean. It is absolutely forbidden to use oxidized ionized water (strongly oxidized water, peroxide water) or disinfectant for cleaning, soaking and wiping.